


## Copper Cable, category 3, 50 pair, U/UTP, CM rated, 1000 m, gray



- Exceptional 100-Ohm series cables for both analog and digital services
- Meets or exceeds industry requirements and environmental regulations
- Small outside diameter and cross-sectional area in bundles and cable
- Innovative design and enhanced electrical and mechanical performance

### Product Classification

<b>Regional Availability</b>	Asia
<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Twisted pair cable
<b>Product Series</b>	310 Series

### General Specifications

<b>ANSI/TIA Category</b>	3
<b>Cable Component Type</b>	Horizontal
<b>Cable Type</b>	U/UTP (unshielded)
<b>Conductor Type, singles</b>	Solid
<b>Conductors, quantity</b>	100
<b>Jacket Color</b>	Gray
<b>Pairs, quantity</b>	50
<b>Transmission Standards</b>	ANSI/TIA-568.2-D   CENELEC EN 50288-6-1   ISO/IEC 11801 Class E

### Dimensions

<b>Cable Length</b>	1,000 m   3,280.84 ft
<b>Diameter Over Jacket, nominal</b>	13.005 mm   0.512 in
<b>Conductor Gauge, singles</b>	26 AWG

### Electrical Specifications

<b>Characteristic Impedance</b>	100 ohm
<b>Characteristic Impedance Tolerance</b>	±15 ohm
<b>dc Resistance, maximum</b>	14 ohms/100 m   4.267 ohms/100 ft

# 5-219580-1

---

<b>Mutual Capacitance at Frequency</b>	5.6 nF/100 m @ 1 kHz
<b>Operating Voltage, maximum</b>	80 V

## Material Specifications

<b>Conductor Material</b>	Bare copper
<b>Insulation Material</b>	Polyolefin
<b>Jacket Material</b>	PVC

## Environmental Specifications

<b>Operating Temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>Storage Temperature</b>	-20 °C to +70 °C (-4 °F to +158 °F)
<b>Flame Test Method</b>	NEC Article 800   UL 444

## Packaging and Weights

<b>Packaging Type</b>	Reel
-----------------------	------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

