


# UHVMPMPAL

## Base Product



Ultra Low Loss (ULL) LazrSPEED® 550 OM5 MPO12(Unpinned) to MPO12(Unpinned), Armored Pre-terminated Trunk Cable, 96-Fiber, Plenum

This product will be discontinued on: April 30, 2024

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   Europe   Latin America   Middle East /Africa   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber trunk cable assembly
<b>Product Brand</b>	SYSTIMAX ULL
<b>Ordering Note</b>	For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration

## General Specifications

<b>Connector A, quantity</b>	8
<b>Color, boot A</b>	Black
<b>Color, connector A</b>	Lime green
<b>Connector B, quantity</b>	8
<b>Color, boot B</b>	Black
<b>Color, connector B</b>	Lime green
<b>Construction Type</b>	Armored   Stranded
<b>Furcation Color</b>	Lime green
<b>Interface, Connector A</b>	MPO-12/UPC Female
<b>Interface Feature, connector A</b>	Unpinned
<b>Interface, Connector B</b>	MPO-12/UPC Female
<b>Interface Feature, connector B</b>	Unpinned
<b>Jacket Color</b>	Lime green
<b>Polarity</b>	Method B Enhanced (ULL)

# UHVMPMPAL

---

**Fibers per Subunit, quantity** 12

**Total Fibers, quantity** 96

## Dimensions

**Breakout Length** 33 in

**Cable Assembly Length Range (m)** 3 – 999

**Cable Assembly Length Range (ft)** 10 – 999

## Mechanical Specifications

**Cable Retention Strength, maximum** 11.24 lb @ 0 ° | 4.40 lb @ 90 °

## Optical Specifications

**Fiber Mode** Multimode

**Fiber Type** OM5, LazrSPEED®

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Environmental Space** Indoor | Plenum

## Included Products

- 760230250 P-096-MZ-5G-F12LM – Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, interlocking aluminum armored with plenum jacket, Multimode OM5, 96 fiber multi-unit with 12 fiber subunits, Lime-green jacket color, Feet cable marking
- 860617232 – MPO12, ULTRA LOW LOSS, FEMALE, OM5, LIME, 3mm