


# MP-PP13M4-16C-120



PIM Optimized Adjustable 4-Sector Monopole Platform with 13ft Face - 2-7/8in OD Face Pipes & Top Rail - Includes (16) 2-7/8in OD x 120in Antenna Pipes

## Product Classification

<b>Product Type</b>	Co-location platform
<b>Product Brand</b>	PIM-guard

## General Specifications

<b>Mounting</b>	Monopole, 381–1143 mm (15–45 in) OD
<b>Pipe, quantity</b>	16
<b>Sectors, quantity</b>	4

## Dimensions

<b>Face Width</b>	3,962 mm   13 ft
<b>Platform Width</b>	3,962.4 mm   156 in
<b>Width</b>	3,962.4 mm   156 in
<b>Pipe Length</b>	3,048 mm   120 in
<b>Face Support Pipe Diameter</b>	73.152 mm   2.88 in
<b>Mounting Diameter, maximum</b>	1,143 mm   45 in
<b>Mounting Diameter, minimum</b>	381 mm   15 in
<b>Pipe Outer Diameter</b>	73.152 mm   2.88 in

## Material Specifications

<b>Material Type</b>	Hot dip galvanized steel
----------------------	--------------------------

## Mechanical Specifications

<b>Wind Rating Test Method</b>	TIA/EIA-222
--------------------------------	-------------

# MP-PP13M4-16C-120

---

## Packaging and Weights

<b>Included</b>	Plain end pipes   Platform   Rail   Ring mount
<b>Packaging quantity</b>	1
<b>Weight, net</b>	2,303.886 kg   5,079.2 lb